
STAND-ALONE "VINOLOK" APPLICATOR









Our solutions for Vinolok glass stoppers, an innovation made by Costral that adapts easily to your machines.

Stand-alone and automatic Vinolok application device with:

- Inert gaz injection in the bottle head-space before closing
- Rotary 5-position dispensing of the glass stopper on the bottle
- Pluging-in-head of the Vinolok stopper

TWO SIMPLE INSTALLATION SOLUTIONS:



A complete system, from supply to application

- Vibrating distributor dedicated to the Vinolok application
- Presence control of Vinolok stopper
- Output up to 4000 BPH
- Automatic corking equipment
- Seal integrity respect
- Integrated safety shielding

A separate and automatic distributor for your glass stoppers types, «Low Top» Ø 18,5 mm or «High Top» Ø 18,5 or 21,5 mm.

This Applicator is carried on a stainless steel foot, with mobile and easy-to-use control panel, adjustable support for the height of the dispensing and pluging-inhead.

Bottles driven thanks to a motorized Archimedes screw, complete vibrating distributor with hopper, automatic dispenser with pushing system and an external foot.





Vinolok equipment to integrate in a monobloc

A distributor with a complete equipment integrated into a COSTRAL machine (or another machine on request).

A complete installation with hopper, CO2 sweeping, vibrating distributor, feeding canal in aluminum with hinge for automatic setting of heights and stopper presence control, rotating capping-head with 5 positions.





Inert gaz solution for the head-space



Application pressure adapted to the Vinolok stopper



The speed at which the stoppers are placed is synchronized with the machine's outlet (up to 4000 BPH)